



Listings / Approvals	
California State Fire Marshal FD-xxx	3225-0981:102
CSFM FDR-xxx	3225-0981: 0112
UL Category EMME	R13317

MODEL	Type	Fire Rating	MOUNT	Max. Single Section Sizes						Max. Multi Section Sizes					
				(W x H, in.)						(W x H, in.)					
				A	B & B2	C & CO	CR	R		A	B & B2	C & CO	CR	R	
Static-Rated Curtain Fire Dampers															
narrowline frame FD-110	Curtain	1.5	H or V	48 x 48	48 x 42	---	---			96 x 48	96 x 42	---	---	---	---
low / medium pressure FD-150	Curtain	1.5	H or V	48 x 48	48 x 42	46 x 41	41	47	46	96 x 48 or 120 x 40	96 x 42 or 120 x 35	94 x 41 or 118 x 34	41	47	46
			V	37 x 37	37 x 32	37 x 31	31	36	35	74 x 74	74 x 69	72 x 68	68	73	72
Kitchen low/medium pressure KFD-150	Curtain	1.5	H or V	36 x 16	---					48 x 48	---				
integral sleeve FD-150x12, FD-150x16	Curtain	1.5	H or V	48 x 48	48 x 42	46 x 41	41	47	46	See FD-150 with a sleeve					
Stainless steel SSFD-150	Curtain	1.5	H	36 x 36	36 x 31	34 x 31	30	35	34	---	---	---	---	---	---
			V	48 x 48	48 x 42	46 x 41	41	31	30	96 x 48 or 120 x 40	96 x 42 or 120 x 35	94 x 41 or 118 x 34	---	47	46
Out of Wall OFD-150	Curtain	1.5	H or V	36 x 36	36 x 31	---	---			---					
narrowline frame FD-310	Curtain	3	V	48 x 48	48 x 42	---	---			---					
low / medium pressure FD-350	Curtain	3	V	48 x 48	48 x 42	46 x 41	41	47	46	---					
			H	40 x 40	40 x 35	38 x 34	34	39	38	80 x 40	80 x 35	78 x 34	---	---	---
Kitchen low/medium pressure KFD-350	Curtain	3	H or V	36 x 16	---					40 x 40	---				
Stainless steel SSFD-350	Curtain	3	V	48 x 48	48 x 42	46 x 41	41	47	46	---					