

Nomenclature Breakdown

1 Model		2 Size		3 Energy Recovery		4 Cooling		5 Heating		6 Unit Information	
RV	Rooftop ventilator	RV		RV		Nominal Tonnage (PDX, ASHP, & RC only)	Cooling Type	0	None	SA Discharge/RA Intake & OA Configuration	
RVE	Rooftop ventilator w/ wheel	10	XS	-		3	I	1	Electric	Revision	
RVC	Rooftop ventilator w/ core	25	S	RVE		4	J	2	Hot water	2 Efficiency Update R-454B	
		45	M	Wheel Diameter (in.)	Wheel Model	5	K	B	75 mbh IG		
		75	L	30	B	6	L	C	100 mbh IG		
				36	C	7	A	E	150 mbh IG		
				41	D	10	B	G	200 mbh IG		
				52	E	12.5	CW	J	300 mbh IG		
				58		15		M	400 mbh IG		
				74		17.5		N	500 mbh IG		
				78		20		O	600 mbh IG		
				81		25		Q	800 mbh IG		
						30		R	1000 mbh IG		
						40		T	1200 mbh IG		
						50					
						60					
						70					

August 2024