





Selection Guide for Dampers



Type	Application	Model	BINDER TAB
Life Safety Dampers 	Fire	FD / DFD Series DFDR Series OFD / ODFD Series	LIFE SAFETY DAMPER PRODUCTS
	Smoke	SMD / SMDR Series	
	Combination Fire-Smoke	FSD / FSDR Series CFSD Series OFSD Series GFSD Series	LIFE SAFETY DAMPER PRODUCTS
	Ceiling Radiation	CRD Series	
Control 	Commercial	VCD / VCDR Series VCDRM Series	CONTROL & BALANCING
	Industrial	HCD / HCDR Series	HEAVY-DUTY / INDUSTRIAL
	Balancing	ABD Series MBD / MBDR Series RBD / RBDR Series	CONTROL & BALANCING
	Insulated/Thermally Broken	ICD Series	
	Air Measuring	AMD / AMS Series	
	Face and Bypass Control	FBV Series	
Access Doors	Access Doors	HAD / CAD / RAD Series	ACCESS DOORS
Pressure Relief Doors	Pressure Relief Doors	PRAD / VRAD Series	
Backdraft 	Exhaust	BD Series EM-10 & EM-30 Series WD-100 & WD-300 Series	BACKDRAFT
	Intake	EM-40 Series WD-200 & WD-400 Series	
	Round	WDR / SSWDR Series	
	Industrial	HB Series	HEAVY-DUTY / INDUSTRIAL AND BACKDRAFT
Relief Dampers	Industrial Pressure	HPR Series	BACKDRAFT
	Barometric	BR Series	
Severe Environment 	Fire	SEDFD Series	LIFE SAFETY DAMPER PRODUCTS
	Combination Fire Smoke	SEFSD Series SEFSDR Series	
	Smoke	SESMD Series SESMDR-501 Series	
	Barometric	SEBR Series	BACKDRAFT
	Commercial Control	SEVCD Series	CONTROL & BALANCING
	Industrial Control	HCD Series	HEAVY-DUTY / INDUSTRIAL
		HCDR Series	
	Industrial Backdraft	HB Series	HEAVY-DUTY / INDUSTRIAL AND BACKDRAFT
Bubble-Tight	Industrial	HBTR Series	BUBBLE-TIGHT
Blast and Tornado	Industrial	HBS / HTOD Series	HEAVY-DUTY/INDUSTRIAL

Selection Guide for Duct Heaters

Duct Heaters 	Duct Heaters	IDHB / IDHE Series	DUCT HEATERS
--	--------------	--------------------	--------------