


Construction

	Standard	Optional
Frame Material	Galvanized steel	-
Frame Material Thickness	16 ga. (1.5mm)	-
Frame Type	5 in. x 1 in. (127mm x 25mm) hat channel	-
Blade Action	Parallel	-
Blade Material	Galvanized steel	-
Blade Material Thickness	16 ga. (1.5mm)	-
Blade Type	3V	-
Blade Orientation	Horizontal	-
Linkage	Plated steel out of airstream, concealed in jamb	-
Axle Bearings	316SS	-
Axle Material	Plated steel	-
Blade Seals	Silicone	-
Jamb Seals	Stainless Steel	-
Closure Device	RRL	RRL/OCI, TOR, Fusible Link
Closure Temperature	165°F (74°C)	212°F (100°C), 250°F (121°C) 286°F (141°C)* 350°F (177°C)
Mounting	Horizontal	Vertical



*Only available with fusible link

Note:

The frames are constructed with reinforced corners. Low profile head and sill are used on sizes less than 17 in. (432 mm) high for lower pressure drop and improved damper performance.

Options

- [BACnet test module - 120V](#)
- [BACnet test module - 24V](#)
- Breakaway connections
- Clean wrap
- [Greenheck test switches \(GTS\)](#)
- [Grille Tabs](#)
- [Momentary test switch](#)
- [OCI \(Open Closed Indicator switch\)](#) - available when fusible link selected
- [Retaining angles](#)
- Sealed transitions and sleeves
- [Smoke detector - No flow](#)
- [Smoke detector - low flow](#)
- Transitions: C, O, R




Figure 5.2

12 in. x 12 in. (305mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.04
1000	0.14
1500	0.31
2000	0.55
2500	0.86
3000	1.24
3500	1.69
4000	2.20

24 in. x 24 in. (610mm x 610mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.02
1000	0.07
1500	0.16
2000	0.29
2500	0.45
3000	0.65
3500	0.89
4000	1.16

36 in. x 36 in. (914mm x 914mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.04
1500	0.09
2000	0.16
2500	0.25
3000	0.36
3500	0.49
4000	0.64

12 in. x 48 in. (305mm x 1219mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.06
1500	0.13
2000	0.23
2500	0.36
3000	0.52
3500	0.70
4000	0.92

48 in. x 12 in. (1219mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.03
1000	0.10
1500	0.23
2000	0.41
2500	0.63
3000	0.91
3500	1.24
4000	1.62




Figure 5.3

12 in. x 12 in. (305mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.02
1000	0.09
1500	0.20
2000	0.36
2500	0.56
3000	0.81
3500	1.10
4000	1.44

24 in. x 24 in. (610mm x 610mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.04
1500	0.09
2000	0.16
2500	0.25
3000	0.35
3500	0.48
4000	0.63

36 in. x 36 in. (914mm x 914mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.03
1500	0.06
2000	0.11
2500	0.17
3000	0.24
3500	0.33
4000	0.42

12 in. x 48 in. (305mm x 1219mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.04
1500	0.10
2000	0.17
2500	0.27
3000	0.39
3500	0.53
4000	0.70

48 in. x 12 in. (1219mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.02
1000	0.07
1500	0.16
2000	0.29
2500	0.45
3000	0.64
3500	0.88
4000	1.14




Figure 5.5

12 in. x 12 in. (305mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.06
1000	0.22
1500	0.50
2000	0.89
2500	1.39
3000	2.00
3500	2.72
4000	3.55

24 in. x 24 in. (610mm x 610mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.03
1000	0.14
1500	0.31
2000	0.54
2500	0.85
3000	1.22
3500	1.66
4000	2.17

36 in. x 36 in. (914mm x 914mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.03
1000	0.12
1500	0.26
2000	0.46
2500	0.73
3000	1.05
3500	1.42
4000	1.86

12 in. x 48 in. (305mm x 1219mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.03
1000	0.13
1500	0.30
2000	0.53
2500	0.83
3000	1.19
3500	1.62
4000	2.11

48 in. x 12 in. (1219mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.04
1000	0.17
1500	0.38
2000	0.67
2500	1.04
3000	1.50
3500	2.05
4000	2.67




Greenheck Fan Corporation certifies that the model CFSD-211 shown herein is licensed to bear the AMCA Seal. The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 511 and comply with the requirements of the AMCA Certified Ratings Programs. The AMCA Certified Ratings Seal applies to air performance ratings only.

Configuration Space Envelopes

CFSD-211 is available in 3 different configurations to accommodate a variety of installation and access requirements. Drawings below illustrate these different configurations and their associated dimensions.

Configuration #1 – Fire Rated Ceiling Is The Finished Ceiling: Actuator (Internal Only) Accessible Through The Grille



'A' Dimension Standard


If damper height is less than 11 in. (279mm) then,

$$A = 12 + \text{grille depth} + \text{OBD}$$

If damper height is greater than or equal to 11 in. (279mm) then,

$$A = 7.188 + \text{grille depth} + \text{OBD}$$

Configuration #2 – Fire Rated Ceiling Is The Finished Ceiling: Actuator (Internal or External) Accessible Above Finished Ceiling




Configuration #2 is for applications where the fire rated ceiling is the finished ceiling but where access to the damper actuator is available from above the finished ceiling. Actuators can be mounted internally or externally. Clearance must be maintained between damper and grille for proper operation.

All dimensions shown are in inches (mm)

	'A' Dimension Standard	Minimum Sleeve Length
When OCI, RRL, or TOR, H dimension less than 11 in. (279mm)	12 (305)	21 (533)
All other dampers	7 3/16 (182)	16 (406)

Minimum Size Internal: 12 in. x 12 in. (305mm x 305mm)

Configuration #3 – Fire Rated Ceiling Is Above The Finished Ceiling: Actuator (Internal or External) Accessible Through Finished Ceiling



Configuration #3 is for applications where the fire rated ceiling is above the finished ceiling. Actuators can be mounted internally or externally.

All dimensions shown are in inches (mm)

	'A' Dimension Standard	Minimum Sleeve Length
When OCI, RRL, or TOR, H dimension less than 11 in. (279mm)	12 (305)	21 (533)
All other dampers	7 3/16 (182)	16 (406)

Minimum Size Internal: 12 in. x 12 in. (305mm x 305mm)



[INSTALLATION](#)



[CATALOG](#)



[SELECTION GUIDE](#)



[ALTERNATE INSTALLATION](#)



[SPECIFICATIONS](#)



[WARRANTY](#)