

### Application

Model DFDR-510 is a dynamic rated round fire damper for use in HVAC systems that are operational in the event of a fire. This fire damper is rated for use in walls, floors, and partitions with less than 3 hour fire resistance rating and can be mounted vertically or horizontally.

### Ratings

#### UL 555 Fire Resistance

Fire Rating: 1½ hours

#### Velocity

2000 fpm (10.2 m/s)

#### Pressure

Maximum: 4 in. wg (1 kPa)

### Construction

	Standard	Optional
<b>Frame Material</b>	Galvanized steel*	-
<b>Frame Material Thickness</b>	20 ga. (1 mm)	16 ga. (1.5 mm)
<b>Blade Material</b>	Galvanized steel	-
<b>Blade Thickness</b>	20 ga. (1mm)	-
<b>Axle Bearings</b>	Bronze	316SS
<b>Axle Material</b>	½ in. (13mm) plated steel	-
<b>Closure Device</b>	Fusible Link	-
<b>Closure Temperature</b>	165° F (74°C)	212°F (100°C) or 286°F (141°C)



\*Dimensions (dia.) are furnished approximately ⅛ in. (3mm) undersize.



See complete marking on product.

UL 555 Classification R13317

Model DFDR-510 meets the requirements for fire dampers established by:


#### National Fire Protection Association

NFPA Standards 80, 90A, & 101

#### International Building Code (IBC)

#### California State Fire Marshall (CFSM)

Fire Damper Listing #3225-0981:0112



### Size Limitations

Diameter	Minimum Size	Maximum Size
Inches	4	24
mm	102	610


Wall Thickness (mm)	Sleeve Length (mm)
Up to 6½ in. (165)	13 ⅝ in. (346)
Up to 8½ in. (216)	15 ⅝ in. (397)
Up to 10½ in. (267)	17 ⅝ in. (448)
Over 10½ in. (267)	Consult Greenheck

## Options

- One retainer plate supplied with damper
- Additional retainer plate available

DFDR-510

Dynamic Rated Round Fire Damper



## Document Links



[INSTALLATION](#)



[CATALOG](#)



[SELECTION GUIDE](#)



[SPECIFICATIONS](#)



[WARRANTY](#)



P.O. Box 410 • Schofield, WI 54476-0410 • 715.359.6171 • [greenheck.com](http://greenheck.com)

Copyright © 2024 Greenheck Fan Corporation

DFDR-510, R19, December 2024

Greenheck Fan Corporation reserves the right to make product changes without notice