

### Application

Model SSDFDR-510 is a dynamic rated round fire damper for use in HVAC systems that are operational in the event of a fire. This fire damper is rated for use in walls or partitions with less than 3 hour fire resistance rating and can be mounted vertically or horizontally.

### Ratings

#### UL 555 Fire Resistance

Fire Rating: 1½ hours

#### Velocity

2000 fpm (10.2 m/s)

#### Pressure

Maximum: 4 in. wg (1 kPa)

### Construction

	Standard	Optional
Frame Material	304SS	-
Frame Material Thickness	20 ga. (1 mm)	-
Blade Material	304SS	-
Blade Material Thickness	20 ga. (1 mm)	-
Axle Bearings	Stainless steel	-
Axle Material	½ in. (13 mm) stainless steel	-
Closure Device	Fusible Link	-
Closure Temperature	165°F (74°C)	212°F (100°C), 286°F (141°C)



Dimensions (dia.) are furnished approximately ⅛ in. (3mm) undersize.



See complete marking on product.  
UL 555 Classification R13317

Model SSDFDR-510 meets the requirements for fire dampers established by:

**National Fire Protection Association**

NFPA Standards 80, 90A, & 101

**International Building Codes (IBC)**


**California State Fire Marshal (CSFM)**

Fire Damper Listing (#3225-0981:0112)

### Size Limitations

Diameter	Minimum Size (mm)	Maximum Size (mm)
Inches	4 (102)	24 (610)


Wall Thickness (mm)	Sleeve Length (mm)
Up to 6½ in. (165)	13 ⅝ in. (346)
Up to 8½ in. (216)	15 ⅝ in. (397)
Up to 10½ in. (267)	17 ⅝ in. (448)
Over 10½ in. (267)	Consult Greenheck



## Options

- One retainer plate supplied with damper
- Additional retainer plate available

## SSDFDR-510 Round Fire Damper



## Document Links



[INSTALLATION](#)



[CATALOG](#)



[SELECTION GUIDE](#)



[SPECIFICATIONS](#)



[WARRANTY](#)



P.O. Box 410 • Schofield, WI 54476-0410 • 715.359.6171 • [greenheck.com](http://greenheck.com)

Copyright © 2024 Greenheck Fan Corporation  
SSDFDR-510, R14, September 2024  
Greenheck Fan Corporation reserves the right to make  
product changes without notice