



Comparison Guide

Dedicated Outdoor Air Systems
Models RV, RVE & RVC



Supply Airflow Capacities Comparison without Energy Recovery



RV-10 Comparison

-  Greenheck Advantage
-  Competitor Advantage
-  Equal Standing

		Greenheck RV-10	Aaon RQ	CaptiveAir HVAC-1	Daikin DPS-Small	Trane OAB
COMPETITIVE PRICING						
Supply Airflow	Min CFM	500	500	500	500	500
	Max CFM	2,500	3,200 	3,000 	2,400	3,000 
Packaged DX Cooling	Min Tons	3	2	3	3	3
	Max Tons	7	6 	7.5	6 	9 
	Tonnage Options	3, 4, 5, 6, 7	2, 3, 4, 5, 6	3, 4, 5, 6, 7.5	3, 4, 5, 6	3, 4, 5, 6, 7, 8, 9
	Lead Compressor Type	Inverter	Two-Stage, Digital, Inverter	Inverter	Inverter	Digital, Inverter
	Quantity of Compressors/Circuits	1 / 1	1 / 1	1 / 1	1 / 1	1 / 1
	Modulating Head Pressure Control (Condensing Fan)	Standard All EC	Standard All AC Optional All EC	Standard All EC	Standard All EC	Standard All AC Optional All EC
Indirect Gas Furnace	Min MBH	75	60 	50 	80	50 
	Max MBH	200	160 	260 	160 	200
	Furnace Size (MBH)	75, 100, 150, 200	60, 100, 140, 160	50, 75, 100, 125, 150, 200, 260	80, 120, 160	50, 75, 100, 125, 150, 200
	High Turndown	Up to 16:1	Up to 12:1	Up to 20:1	Up to 5:1	Up to 20:1
Unit Construction		2" R13 injected foam insulation Standard 2" base insulation	2" R13 injected foam insulation Standard no base insulation (optional) 	1" R4.3 fiber glass duct board insulation No base insulation 	1" R7 injected foam insulation Standard 1" base insulation 	2" R13 foam board insulation Standard 2" base insulation 
Unit Coating		Standard Exterior Coating	Standard Exterior Coating	Standard Galvanized Steel Optional Exterior Coating 	Standard Exterior Coating	Standard Exterior Coating
Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)		82 x 44 x 58 ^A	82 x 44 x 51 ^A	77 x 62 x 48 ^A	67 x 54 x 41 ^A	97 x 52 x 55 ^A
Weight (approx. pounds)		1,180	1,130	1,200	1,440 	1,806 
Supply Discharge Option		Bottom or Side ^B	Bottom or Side	Bottom, Side, Top ^B	Bottom or Horizontal	Bottom or Side ^B
Return Intake Option		Bottom or End ^B	Bottom or Side	Bottom or Side	Bottom or End	Bottom or Side ^B

^A Not including side condensing section or weatherhood when applicable

^B Dependent on unit configuration and options

RV-25 Comparison

-  Greenheck Advantage
 Competitor Advantage
 Equal Standing

		Greenheck RV-25	Aaon		CaptiveAir		Daikin	Trane	Trane
			RN-A	RN-B	HVAC-2	HVAC-3	DPS - Medium	OAD	OAB
COMPETITIVE PRICING									
Supply Airflow	Min CFM	500	1,000	1,300	800	1,250	750	1,250	500
	Max CFM	6,500	5,500 	7,500 	4,000 	8,000 	6,000 	8,000 	3,000 
Packaged DX Cooling	Min Tons	5	6	9	8	12.5	7	10	3
	Max Tons	15	10 	15	10 	30 	17	30 	9 
	Tonnage Options	5, 7, 10, 12.5, 15	6, 7, 8, 10	9, 11, 13, 15	8, 10	12.5, 15, 20, 30	7, 10, 12, 15	10, 12, 15, 17, 20, 25, 30	3, 4, 5, 6, 7, 8, 9
	Lead Compressor Type	Inverter	Two-Stage, Digital, Inverter		Inverter		Inverter	Standard, Digital 	Standard, Digital, Inverter
	Quantity of Compressors/Circuits	1 / 1	1 / 1	2 / 2	1 / 1		1 / 1	2 / 1	1 / 1
	Modulating Head Pressure Control (Condensing Fan)	Standard Lead EC Optional All EC	Standard All AC Optional All EC or VFD		Standard All EC		Standard All EC	Standard All AC Optional All EC or VFD	
Air-Source Heat Pump	Min Tons	5	6	9	8	12.5	7.5	10	3
	Max Tons	15	10 	15	10 	30 	15	20 	9 
	Tonnage Options	5, 7, 10, 12.5, 15	6, 7, 8, 10	9, 11, 13, 15	8, 10	12.5, 15, 20, 30	7, 10, 12, 15	10, 12, 15, 17, 20	3, 4, 5, 6, 7, 8, 9
	Lead Compressor Type	Inverter	Digital 		Inverter		Inverter	Digital 	Digital, Inverter
	Quantity of Compressors/Circuits	1 / 1 (5-7.5 tons) 2 / 2 (10-15 tons)	1 / 1	2 / 2	1 / 1		1 / 1	2 / 1	1 / 1
	ASHP Lockout (°F)	0°	0°		9° 		0°	0°	
	Secondary Heat Options	Electric, Indirect Gas, Hot Water	Electric, Indirect Gas, Hot Water		Electric, Indirect Gas		Electric, Indirect Gas, Hot Water	Electric, Indirect Gas, Hot Water	Electric
Indirect Gas Furnace	Min MBH	100	90	195	50	150	200	50	
	Max MBH	300	210 	390 	440 	685 	400 	350 	200 
	Furnace Size (MBH)	100, 200, 300	90, 150, 210	195, 292, 390	50, 100, 150, 200, 250, 300, 440	150, 200, 250, 300, 400, 500, 685	200, 300, 400	50, 75, 100, 125, 150, 200, 250, 300, 350	50, 75, 100, 125, 150, 200
	High Turndown	Up to 16:1	Up to 11:1	Up to 10:1	Up to 21:1	Up to 25:1	Up to 10:1	Up to 20:1	
Unit Construction		2" R13 injected foam insulation Standard 2" base insulation	2" R13 injected foam insulation Standard no base insulation (optional) 		2" R13 foam board insulation No base insulation 		1" R7 injected foam insulation Std. 1" base insulation 	2" R13 foam board insulation Standard 2" base insulation	
Unit Coating		Standard Exterior Coating	Standard Exterior Coating		Standard Galvanized Steel Optional Exterior Coating 		Standard Exterior Coating	Standard Exterior Coating	
Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)		99 x 52 x 59 ^A	82 x 44 x 44 ^A	88 x 59 x 50 ^A	82x 81 x 61 ^A	97 x 90 x 61 ^A	91 x 58 x 56 ^A	110 x 63 x 69 ^A	97 x 52 x 55 ^A
Weight (approx. pounds)		2,700	1,400 	2,600	1,730 	3,000	2,403	3,975 	1,806
Supply Discharge Option		Bottom or Side ^B	Bottom 		Bottom, Side, Top ^B		Bottom 	Bottom or Side ^B	
Return Intake Option		Bottom, End, Side ^B	Bottom 		Bottom or Side		Bottom 	Bottom or Side ^B	

^A Not including side condensing section or weatherhood when applicable

^B Dependent on unit configuration and options

RV-45 Comparison

-  Greenheck Advantage
 Competitor Advantage
 Equal Standing

		Greenheck RV-45	Aaon RN-C	CaptiveAire HVAC-3 HVAC-4		Daikin DPS - Large	Trane OAD
COMPETITIVE PRICING			=	=	⚠	=	=
Supply Airflow	Min CFM	500	2,000	1,250	2,200	1,500	1,250
	Max CFM	12,500	12,600 ⚠	8,000 	15,000 ⚠	10,500	8,000 
Packaged DX Cooling	Min Tons	15	11	12.5	22.5	16	10
	Max Tons	30	30	30	60 ⚠	31 ⚠	30
	Tonnage Options	15, 17.5, 20, 25, 30	11, 13, 16, 18, 20, 25, 30	12.5, 15, 20, 30	22.5, 25, 30, 40, 50, 60	16, 18, 20, 25, 30, 31	10, 12, 15, 17, 20, 22, 25, 30
	Lead Compressor Type	Inverter	Two-Stage, Digital, Inverter	Inverter		Inverter	Standard, Digital
	Quantity of Compressors/Circuits	1 / 1 (15-17.5 tons) 2 / 1 (20-30 tons)	1 / 1 (16 tons) 2 / 2	1 / 1	1 / 1 (22-30 tons) 2 / 2 (40-60 tons)	1 / 1 (16-20 tons) 2 / 2 (25-31 tons)	2 / 2
	Modulating Head Pressure Control (Condensing Fan)	Standard Lead EC Optional All EC	Standard All AC Optional All EC or VFD	Standard All EC		Standard All EC	Standard All AC Optional All EC or VFD
Air-Source Heat Pump	Min Tons	15	14	12.5	22.5 ⚠	16	Option not available 
	Max Tons	30	30	20 	30	20 	
	Tonnage Options	15, 17.5, 20, 25, 30	14, 16, 18, 20, 25, 30	12.5, 15, 20	22.5, 25, 30	16, 18, 20	
	Lead Compressor Type	Inverter	Digital 	Inverter		Inverter	
	Quantity of Compressors/Circuits	2 / 2	2 / 2	1 / 1		1 or 2	
	ASHP Lockout (°F)	0°	0°	9° 		0°	
Indirect Gas Furnace	Secondary Heat Options	Electric, Indirect Gas, Hot Water	Electric, Indirect Gas, Hot Water	Electric, Indirect Gas		Electric, Indirect Gas, Hot Water	
	Min MBH	300	270	150	200	300	100
	Max MBH	600	540 	685 ⚠	800 ⚠	600	600
	Furnace Size (MBH)	300, 400, 500	270, 405, 540	150, 200, 250, 300, 400, 500, 685	200, 300, 400, 500, 600, 700, 800	300, 450, 600	100, 125, 150, 200, 250, 300, 350, 400, 500, 600
High Turndown		Up to 15:1	Up to 18:1	Up to 25:1	Up to 18:1	Up to 12:1	Up to 20:1
Unit Construction		2" R13 injected foam insulation Standard 2" base insulation	2" R13 injected foam insulation Standard no base insulation (optional) 	2" R13 foam board insulation No base insulation 		2" R13 injected foam insulation Standard 2" base insulation	2" R13 foam board insulation Standard 2" base insulation 
Unit Coating		Standard Exterior Coating	Standard Exterior Coating	Standard Galvanized Steel Optional Exterior Coating 		Standard Exterior Coating	Standard Exterior Coating
Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)		109 x 68 x 73 ^A	138 x 64 x 60 ^A	99 x 90 x 61 ^A	174 x 90 x 94 ^A	77 x 125 x 71 ^A	121 x 74 x 67 ^A
Weight (approx. pounds)		4,500	4,000	2,650 ⚠	6,250 	3,990	3,975
Supply Discharge Option		Bottom or Side ^B	Bottom or End	Bottom, Side, Top ^B		Bottom or Horizontal	Bottom or Side ^B
Return Intake Option		Bottom, End, Side ^B	Bottom, End, Side	Bottom or Side		Bottom 	Bottom or Side ^B

^A Not including side condensing section or weatherhood when applicable

^B Dependent on unit configuration and options

RV-75 Comparison

 Greenheck Advantage

 Competitor Advantage


 Equal Standing

		Greenheck RV-75	Aaon RN-D	CaptiveAir HVAC-4	Daikin DPSA - B	Daikin DPSA - C	Trane OAND	Trane Horizon OANG
COMPETITIVE PRICING								
Supply Airflow	Min CFM	3,750	4,300	2,200	5,000	5,000	3,750	5,000
	Max CFM	18,000	28,400 	15,000 	21,000 	27,000 	13,500 	25,000 
Packaged DX Cooling	Min Tons	25	26	22.5	30	45	30	40
	Max Tons	70	70	60 	52 	75 	60 	80 
	Tonnage Options	25, 30, 40, 50, 60, 70	26, 31, 40, 50, 60, 70	22.5, 25, 30, 40, 50, 60	31, 34, 35, 40, 45, 50, 52	45, 55, 60, 68, 75	30, 35, 40, 45, 50, 54	40, 45, 50, 55, 60, 65, 70, 75, 80
	Lead Compressor Type	Inverter	Digital, Inverter	Inverter	Five-Stage, Inverter	Inverter, Standard	Digital, Inverter	Digital 
	Quantity of Compressors/Circuits	2 / 2 (25-30 tons) 3 / 2 (40 tons) 4 / 2 (50-70 tons)	2 / 2	1 / 1 (22.5-30 tons) 2 / 2 (40-60 tons)	2 / 2 4 / 2	4 / 2	2 / 2 (30 tons) 3 / 2 (35-45 tons) 4 / 2 (50-54 tons)	4 / 2 (40-70 tons) 4-6 / 2 (80 tons)
	Modulating Head Pressure Control (Condensing Fan)	Standard Lead EC Optional All EC	Standard All AC Optional All EC or VFD	Standard All EC	Standard Lead VFD Optional All VFD	Standard All AC Optional Lead VFD 	Standard All AC Optional All EC or VFD 	
Indirect Gas Furnace	Min MBH	600	600	200 	200 	400 	300 	300 
	Max MBH	1,200	1,200	800 	1,125 	1,500 	1,000 	1,200
	Furnace Size (MBH)	600, 800, 1000, 1,200	600, 900, 1,200	200, 300, 400, 500, 600, 700, 800	200, 400, 600, 800, 1,125	400, 600, 800, 1,125, 1,500	300, 350, 400, 500, 600, 700, 800, 1,000	300, 350, 400, 500, 600, 800, 1,000, 1,200
	High Turndown	Up to 16:1	Up to 20:1	Up to 18:1	Up to 20:1		Up to 20:1	
Unit Construction		2" R13 injected foam insulation Standard 2" base insulation	2" R13 injected foam insulation Standard no base insulation (optional) 	2" R13 foam board insulation No base insulation 	2" R13 injected foam insulation Standard 2" base insulation 		2" R13 foam board insulation Standard 2" base insulation 	
Unit Coating		Standard Exterior Coating	Standard Exterior Coating	Standard Galvanized Steel Optional Exterior Coating 	Standard Exterior Coating		Standard Exterior Coating	
Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)		155 x 98 x 101 ^A	161 x 100 x 102 ^A	174 x 90 x 94 ^A	245 x 97 x 78 ^A	No published data	144 x 67 x 92 ^A	182 x 98 x 108 ^A
Weight (approx. pounds)		6,500	6,800	6,250	6,900	No published data	7,014 	9,618 
Supply Discharge Option		Bottom or Side	Bottom 	Bottom, Side, Top ^B	Bottom, Side, Top		Bottom or Side ^B	
Return Intake Option		Bottom, End, Side ^B	Bottom 	Bottom or Side	Bottom or End ^B	Bottom or End	Bottom or Side ^B	

^A Not including side condensing section or weatherhood when applicable

^B Dependent on unit configuration and options

Supply Airflow Capacities Comparison with Energy Recovery



RVE-20 Comparison

-  Greenheck Advantage
 Competitor Advantage
 Equal Standing

		Greenheck RVE-20	Aaon RQ	CaptiveAire HVAC - 1	Daikin DPS - Small	Trane OABD
COMPETITIVE PRICING						
Supply Airflow	Min CFM	500	500	No published data available	500	500
	Max CFM	2,000	3,200 		2,400 	3,000 
Outdoor Airflow	Min CFM	500	500		500	500
	Max CFM (No Wheel Bypass)	2,000	1,900 		1,500 	3,000 
Packaged DX Cooling	Min Tons	3	2		3	3
	Max Tons	7	6 		6 	9 
	Tonnage Options	3, 4, 5, 6, 7	2, 3, 4, 5, 6		3, 4, 5, 6	3, 4, 5, 6, 7, 8, 9
	Lead Compressor Type	Inverter	Two-Stage, Digital, Inverter		Inverter	Standard, Digital, Inverter
	Quantity of Compressors/Circuits	1 / 1	1 / 1		1 / 1	1 / 1
	Modulating Head Pressure Control (Condensing Fan)	Standard All EC	Standard All AC Optional All EC or VFD		Standard All EC	Standard All AC Optional All EC or VFD
Air-Source Heat Pump	Min Tons	3	2		3	Option not available
	Max Tons	7	6 		6 	
	Tonnage Options	3, 4, 5, 6, 7	2, 3, 4, 5, 6		3, 4, 5, 6	
	Lead Compressor Type	Inverter	Two-Stage, Digital, Inverter		Inverter	
	Quantity of Compressors/Circuits	1 / 1	1 / 1		1 / 1	
	ASHP Lockout (°F)	0°	0°		0°	
Indirect Gas Furnace	Secondary Heat Options	Electric, Indirect Gas, Hot Water	Electric, Indirect Gas, Hot Water		Electric, Indirect Gas, Hot Water	
	Min MBH	75	60 		80	50 
	Max MBH	200	160 		160 	200
	Furnace Size (MBH)	75, 100, 150, 200	60, 100, 140, 160		80, 120, 160	50, 75, 100, 125, 150, 200
High Turndown		Up to 16:1	Up to 12:1		Up to 5:1	Up to 20:1
Unit Construction		2" R13 injected foam insulation Standard 2" base insulation	2" R13 injected foam insulation Standard no base insulation (optional) 		1" R7 injected foam insulation Standard 1" base insulation 	2" R13 foam board insulation Standard 2" base insulation 
Unit Coating		Standard Exterior Coating	Standard Exterior Coating		Standard Exterior Coating	Standard Exterior Coating
Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)		82 x 44 x 58 ^A	82 x 44 x 51 ^A		86 x 54 x 41 ^A	97 x 52 x 55 ^A
Weight (approx. pounds)		1,180	1,130 		1,440 	1,780 
Supply Discharge Option		Bottom or Side ^B	Bottom or Side		Bottom or Horizontal	Bottom or Side ^B
Return Intake Option		Bottom or End ^B	Bottom or Side		Bottom or End	Bottom or Side ^B
Energy Wheel (Material Type)		Polymer	Polymer or Aluminum		Polymer	Polymer or Aluminum

^A Not including side condensing section or weatherhood when applicable

^B Dependent on unit configuration and options

RVE-40 Comparison

-  Greenheck Advantage
 Competitor Advantage
 Equal Standing

Competitor Advantage Equal Standing		Greenheck RVE-40	Aaon		CaptiveAir HVAC - 1/2/3	Daikin		Trane	
			RN-A	RN-B		DPS - Small	DPS - Medium	OAB	OADG
COMPETITIVE PRICING			⚠	=	🏠	⚠	=	=	⚠
Supply Airflow	Min CFM	500	1,000	1,300	No published data available	500	750	500	1,250
	Max CFM	6,500	5,500 🏠	7,500 ⚠		2,400 🏠	6,000 🏠	3,000 🏠	8,000 ⚠
Outdoor Airflow	Min CFM	500	1,000	1,300		500	750 🏠	500	1,250
	Max CFM (No Wheel Bypass)	4,400	2,000 🏠	3,300 🏠		1,500 🏠	5,000 ⚠	3,000 🏠	6,750 ⚠
Packaged DX Cooling	Min Tons	5	6	9		3 ⚠	7	3 ⚠	10
	Max Tons	15	10 🏠	15		6 🏠	15	9 🏠	30 ⚠
	Tonnage Options	5, 7, 10, 12.5, 15	6, 7, 8, 10	9, 11, 13, 15		3, 4, 5, 6	7, 10, 12, 15	3, 4, 5, 6, 7, 8, 9	10, 12, 15, 17, 20, 25, 30
	Lead Compressor Type	Inverter	Two-Stage, Digital, Inverter			Inverter		Digital, Inverter	Digital 🏠
	Quantity of Compressors/Circuits	1 / 1	1 / 1	2 / 2		1 / 1		1 / 1	2 / 1
	Modulating Head Pressure Control (Condensing Fan)	Standard Lead EC Optional All EC	Standard All AC Optional All EC or VFD			Standard All EC		Standard All AC Optional All EC or VFD	
Air-Source Heat Pump	Min Tons	5	6	9		3 ⚠	7.5	3	10 🏠
	Max Tons	15	10 🏠	15		6 🏠	15	9	20 ⚠
	Tonnage Options	5, 7.5, 10, 12.5, 15	6, 7, 8, 10	9, 11, 13, 15		3, 4, 5, 6	7, 10, 12, 15	3, 4, 5, 6, 7, 8, 9	10, 12, 15, 17, 20
	Lead Compressor Type	Inverter	Digital 🏠			Inverter		Standard, Digital, Inverter	Digital 🏠
	Quantity of Compressors/Circuits	1 / 1	1 / 1	2 / 2		1 / 1		1 / 1	2 / 1
	ASHP Lockout (°F)	0°	0°			0°		0°	
Indirect Gas Furnace	Secondary Heat Options	Electric, Indirect Gas, Hot Water	Electric, Indirect Gas, Hot Water			Electric, Indirect Gas, Hot Water		Electric 🏠	Electric, Indirect Gas, Hot Water
	Min MBH	100	90	195		80	200	50	
	Max MBH	300	210 🏠	390 ⚠		160 🏠	400 ⚠	200 🏠	350 ⚠
	Furnace Size (MBH)	100, 200, 300	90, 150, 210	195, 292.5, 390		80, 120, 160	200, 300, 400	50, 75, 100, 125, 150, 200	50, 75, 100, 125, 150, 200 250, 300, 350
	High Turndown	Up to 16:1	Up to 11:1	Up to 10:1		Up to 5:1	Up to 10:1	Up to 20:1	
Unit Construction		2" R13 injected foam insulation Standard 2" base insulation	2" R13 injected foam insulation Standard no base insulation (optional) 🏠			1" R7 injected foam insulation Standard 1" base insulation 🏠		2" R13 foam board insulation Standard 2" base insulation 🏠	
Unit Coating		Standard Exterior Coating	Standard Exterior Coating			Standard Exterior Coating		Standard Exterior Coating	
Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)		150 x 53 x 59 ^A	116 x 44 x 44 ^A	128 x 59 x 50 ^A		86 x 54 x 41 ^A	111 x 58 x 56 ^A	119 x 52 x 55 ^A	212 x 63 x 69 ^A
Weight (approx. pounds)		3,400	1,500 ⚠	2,610 ⚠		1,600 ⚠	2,700 ⚠	1,780 ⚠	5,344 🏠
Supply Discharge Option		Bottom or Side ^B	Bottom 🏠			Bottom 🏠		Bottom or Side ^B	
Return Intake Option		Bottom or Side ^B	Bottom 🏠			Bottom 🏠		Bottom or Side ^B	
Energy Wheel (Material Type)		Polymer or Aluminum	Polymer or Aluminum			Polymer		Polymer or Aluminum	

^A Not including side condensing section or weatherhood when applicable

^B Dependent on unit configuration and options

RVE-85 Comparison

-  Greenheck Advantage
 Competitor Advantage
 Equal Standing

		Greenheck RVE-85	Aaon RN-C	CaptiveAir HVAC-3 / 4	Daikin DPS - Large	Trane OAGD
COMPETITIVE PRICING			=		=	=
Supply Airflow	Min CFM	1,250	2,000	No published data available	1,500	1,250
	Max CFM	10,000	12,600 		10,500 	7,500 
Outdoor Airflow	Min CFM	1,250	2,000		1,500	1,470
	Max CFM (No Wheel Bypass)	9,000	6,600 		6,500 	7,350 
Packaged DX Cooling	Min Tons	15	11		16	10
	Max Tons	30	30		28 	30
	Tonnage Options	15, 17.5, 20, 25, 30	11, 13, 16, 18, 20, 25, 30		16, 18, 20, 25, 28	10, 12, 15, 17, 20, 22, 25, 30
	Lead Compressor Type	Inverter	Two-Stage, Digital, Inverter		Inverter	Digital, Inverter
	Quantity of Compressors/Circuits	1 / 1 (15-17.5 tons) 2 / 1 (20-30 tons)	2 / 2		1 / 1 (16-20 tons) 2 / 1 (25-28 tons)	2 / 2
	Modulating Head Pressure Control (Condensing Fan)	Standard Lead EC Optional All EC	Standard All AC Optional All EC or VFD		Standard All EC	Standard All AC Optional All EC or VFD
Air-Source Heat Pump	Min Tons	15	14		16	10
	Max Tons	30	30		20 	20 
	Tonnage Options	15, 17.5, 20, 25, 30	14, 16, 18, 20, 25, 30		16, 18, 20	10, 12, 15, 17, 20
	Lead Compressor Type	Inverter	Digital 		Inverter	Digital, Inverter
	Quantity of Compressors/Circuits	1 / 1 (15-17.5 tons) 2 / 1 (20-30 tons)	2 / 2		1 or 2	2 / 2
	ASHP Lockout (°F)	0°	0°		0°	0°
Indirect Gas Furnace	Secondary Heat Options	Electric, Indirect Gas Hot Water	Electric, Gas, Hot Water		Electric, Indirect Gas, Hot Water,	Electric, Indirect Gas, Hot Water 
	Min MBH	300	270		300	100
	Max MBH	500	540 		600 	600 
	Furnace Size (MBH)	300, 400, 500	270, 405, 540		300, 450, 600	100, 125, 150, 200, 250, 300, 350, 400, 500, 600
High Turndown		Up to 15:1	Up to 18:1		Up to 12:1	Up to 20:1
Unit Construction		2" R13 injected foam insulation Standard 2" base insulation	2" R13 injected foam insulation Standard no base insulation (optional) 		2" R13 injected foam insulation Standard 2" base insulation	2" R13 foam board insulation Standard 2" base insulation
Unit Coating		Standard Exterior Coating	Standard Exterior Coating		Standard Exterior Coating	Standard Exterior Coating
Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)		163 x 68 x 73 ^A	199 x 64 x 59 ^A		206 x 77 x 71 ^A	169 x 74 x 67 ^A
Weight (approx. pounds)		5,100	4,000 		4,620 	5,975 
Supply Discharge Option		Bottom or Side ^B	Bottom or End		Bottom or Horizontal	Bottom or Side ^B
Return Intake Option		Bottom or Side	Bottom, End, Side		Bottom 	Bottom or Side ^B
Energy Wheel (Material Type)		Polymer or Aluminum	Polymer or Aluminum		Polymer	Polymer or Aluminum

^A Not including side condensing section or weatherhood when applicable

^B Dependent on unit configuration and options

RVE-150 Comparison


-  Greenheck Advantage
 Competitor Advantage
 Equal Standing

		Greenheck RVE-150	Aaon RN-D	CaptiveAir HVAC-4	Daikin DPSA - B	Trane OAND	Trane Horizon OANG
COMPETITIVE PRICING			⊖		⊖		
Supply Airflow	Min CFM	3,750	4,300	No published data available	5,000	3,750	5,000
	Max CFM	18,000	28,400 		21,000 	13,500 	25,000 
Outdoor Airflow	Min CFM	2,400	4,300		No published data	No published data	
	Max CFM (No Wheel Bypass)	16,000	12,000 		No published data	No published data	
Packaged DX Cooling	Min Tons	25	26		30	30	40
	Max Tons	70	70		52 	60 	80 
	Tonnage Options	25, 30, 40, 50, 60, 70	26, 31, 40, 50, 60, 70		31, 35, 40, 50, 52	30, 35, 40, 45, 50, 54, 60	40, 45, 50, 55, 60, 65, 70, 75, 80
	Lead Compressor Type	Inverter	Digital, Inverter		Five-Stage, Inverter	Digital, Inverter	Digital 
	Quantity of Compressors/Circuits	2 / 2 (25-30 tons) 3 / 2 (40 tons) 4 / 2 (50-60-70 tons)	4 / 4		2 / 2 4 / 2	2 / 2 (30 tons) 3 / 2 (35-45 tons) 4 / 2 (50-54-60 tons)	4 / 2 (40-70 tons) 4-6 / 2 (80 tons)
	Modulating Head Pressure Control (Condensing Fan)	Standard Lead EC Optional All EC	Standard All AC Optional All EC or VFD		Standard Lead VFD Optional All VFD	Standard All AC Optional All EC or VFD	
Indirect Gas Furnace	Min MBH	600	600		200 	300 	
	Max MBH	1,200	1,200		1,125	1,000 	1,200
	Furnace Size (MBH)	600, 800, 1,000, 1,200	600, 900, 1,200		200, 400, 600, 800, 1,125	300, 350, 400, 500, 600, 700, 800, 1,000	300, 350, 400, 500, 600, 800, 1,000, 1,200
	High Turndown	Up to 16:1	Up to 20:1		Up to 20:1	Up to 20:1	
Unit Construction		2" R13 injected foam insulation Standard 2" base insulation	2" R13 injected foam insulation Standard no base insulation (optional)		2" R13 injected foam insulation Standard 2" base insulation	2" R13 foam board insulation Standard 2" base insulation	
Unit Coating		Standard Exterior Coating	Standard Exterior Coating		Standard Exterior Coating	Standard Exterior Coating	
Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)		200 x 98 x 101 ^A	209 x 100 x 102 ^A		293 x 97 x 78 ^A	239 x 101 x 92 ^A	182 x 98 x 108 ^A
Weight (approx. pounds)		8,000	8,320		10,500 	9,581	9,618
Supply Discharge Option		Bottom or Side	Bottom 		Bottom, Right, Left, Top ^B	Bottom or Side ^B	
Return Intake Option		Bottom or Side	Bottom 		Bottom, End, Side ^B	Bottom or Side ^B	
Energy Wheel (Material Type)		Polymer or Aluminum	Polymer or Aluminum		Aluminum 	Polymer or Aluminum	

^A Not including side condensing section or weatherhood when applicable

^B Dependent on unit configuration and options

Supply Airflow Capacities Comparison with Energy Recovery



RVC-35 Comparison

-  Greenheck Advantage
 Competitor Advantage
 Equal Standing

		Greenheck RVC-35	Aaon RQ	CaptiveAire HVAC	Daikin DPS - Medium	Trane OAB
COMPETITIVE PRICING						
Supply Airflow	Min CFM	500	500		750	
	Max CFM	6,500	3,200 		6,000 	
Outdoor Airflow	Min CFM	500	500		750	
	Max CFM	3,650	1,900 		6,000 	
Packaged DX Cooling	Min Tons	5	2 		7 	
	Max Tons	15	6 		15	
	Tonnage Options	5, 7, 10, 12.5, 15	2, 3, 4, 5, 6		7, 10, 12, 15	
	Lead Compressor Type	Inverter	Two-Stage, Digital, Inverter		Inverter	
	Quantity of Compressors/Circuits	1 / 1	1 / 1		1 / 1	
	Modulating Head Pressure Control (Condensing Fan)	Standard Lead EC Optional All EC	Standard All AC Optional All EC		Standard All EC	
Air-Source Heat Pump	Min Tons	5	2 		7 	
	Max Tons	15	6 		15	
	Tonnage Options	5, 7.5, 10, 12.5, 15	2, 3, 4, 5, 6		7, 10, 12, 15	
	Lead Compressor Type	Inverter	Two-Stage, Digital 		Inverter	
	Quantity of Compressors/Circuits	1 / 1	1 / 1		1 / 1	
	ASHP Lockout (°F)	0°	0°		0°	
Indirect Gas Furnace	Secondary Heat Options	Electric, Indirect Gas, Hot Water	Electric, Indirect Gas, Hot Water		Electric, Indirect Gas, Hot Water	
	Min MBH	100	60 		200 	
	Max MBH	300	160 		400 	
	Furnace Size (MBH)	100, 200, 300	60, 100, 140, 160		200, 300, 400	
		High Turndown	Up to 16:1		Up to 10:1	
Unit Construction		2" R13 injected foam insulation Standard 2" base insulation	2" R13 injected foam insulation Standard no base insulation (optional) 		1" R7 injected foam insulation Standard 1" base insulation 	
Unit Coating		Standard Exterior Coating	Standard Exterior Coating		Standard Exterior Coating	
Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)		181 x 53 x 59 ^A	117 x 44 x 51 ^A		181 x 58 x 57 ^A	
Weight (approx. pounds)		3,800	1,350 		3,863	
Supply Discharge Option		Bottom or Side ^B	Bottom or Side		Bottom	
Return Intake Option		Bottom	Bottom or Side 		Bottom	
Enthalpy Cores	Material Type	Fiber or Polymer	Polymer		Polymer	
	Core Bypass Option	Yes	Yes		Yes	

^A Not including side condensing section or weatherhood when applicable

^B Dependent on unit configuration and options

 Greenheck Advantage
 Competitor Advantage
 Equal Standing

		Greenheck RVC-65	Aaon RN	CaptiveAire HVAC	Daikin DPS - Large	Trane OAB
COMPETITIVE PRICING						
Supply Airflow	Min CFM	1,500	Option not available	Option not available	1,500	Option not available
	Max CFM	10,000			10,500 	
Outdoor Airflow	Min CFM	1,500			1,500	
	Max CFM	6,500			7,000 	
Packaged DX Cooling	Min Tons	15			16	
	Max Tons	30			28 	
	Tonnage Options	15, 17.5, 20, 25, 30			16, 18, 20, 25, 28	
	Lead Compressor Type	Inverter			Inverter	
	Quantity of Compressors/Circuits	1 / 1 (15-17.5 tons) 2 / 1 (20-30 tons)			1 / 1 (16-20 tons) 2 / 1 (25-28 tons)	
	Modulating Head Pressure Control (Condensing Fan)	Standard Lead EC Optional All EC			Standard All EC	
Air-Source Heat Pump	Min Tons	15			16	
	Max Tons	30			20 	
	Tonnage Options	15, 17.5, 20, 25, 30			16, 18, 20	
	Lead Compressor Type	Inverter			Inverter	
	Quantity of Compressors/Circuits	1 / 1 (15-17.5 tons) 2 / 1 (20-30 tons)			1 / 1	
	ASHP Lockout (°F)	0°			0°	
Indirect Gas Furnace	Secondary Heat Options	Electric, Indirect Gas, Hot Water			Electric, Indirect Gas, Hot Water	
	Min MBH	300			300	
	Max MBH	500			600 	
	Furnace Size (MBH)	300, 400, 500			300, 450, 600	
	High Turndown	Up to 15:1			Up to 10:1	
	Unit Construction	2" R13 injected foam insulation Standard 2" base insulation			2" R13 injected foam insulation Standard 2" base insulation	
	Unit Coating	Standard Exterior Coating			Standard Exterior Coating	
	Unit Base Dimensions (bottom connections) (LxWxH - approx. inches)	197 x 68 x 73 ^A			77 x 223 x 71 ^A	
	Weight (approx. pounds)	5,675			6,480 	
	Supply Discharge Option	Bottom or Side ^B			Bottom or Horizontal	
	Return Intake Option	Bottom			Bottom	
Enthalpy Cores	Material Type	Fiber or Polymer			Polymer	
	Core Bypass Option	Yes			Yes	

^A Not including side condensing section or weatherhood when applicable
^B Dependent on unit configuration and options