

|                                |                            | Models                                                     |              |              |                         |
|--------------------------------|----------------------------|------------------------------------------------------------|--------------|--------------|-------------------------|
|                                |                            | RV (10, 25, 45, 75)   RVE (20, 40, 85, 150)   RVC (35, 65) |              |              |                         |
|                                | Housing Size               | 10   20                                                    | 25   35   40 | 45   65   85 | 75   150                |
| AIRFLOW                        | Minimum <sup>a</sup> (CFM) | 500                                                        | 500          | 500          | 3,750                   |
|                                | Maximum <sup>a</sup> (CFM) | 2,500                                                      | 6,500        | 12,500       | 18,000                  |
| COOLING TYPE                   | Packaged direct expansion  | Tons                                                       | Tons         | Tons         | Tons                    |
|                                |                            | 3                                                          | 5            | 15           | 25                      |
|                                |                            | 4                                                          | 7            | 17.5         | 30                      |
|                                |                            | 5                                                          | 10           | 20           | 40                      |
|                                |                            | 6                                                          | 12.5         | 25           | 50                      |
|                                |                            | 7                                                          | 15           | 30           | 60 and 70               |
|                                |                            | Circuits                                                   | Circuits     | Circuits     | Circuits                |
|                                |                            | 1                                                          | 1            | 1            | 2                       |
|                                | Chilled water              | Options                                                    | Option       | Option       | Option                  |
|                                | Air-source heat pump       | -                                                          | Option       | Option       | -                       |
|                                | No cooling                 | Option                                                     | Option       | Option       | Option                  |
| PACKAGED DX COOLING COMPONENTS | Inverter scroll compressor | Standard                                                   | Standard     | Standard     | Standard                |
|                                | Modulating hot gas reheat  | Option                                                     | Option       | Option       | Option                  |
|                                | Lead EC condensing fan     | Standard                                                   | Standard     | Standard     | Standard                |
|                                | All EC condensing fans     | -                                                          | Option       | Option       | Option                  |
| INDIRECT GAS FURNACE           | Minimum (MBH)              | 75                                                         | 100          | 300          | 600                     |
|                                | Maximum (MBH)              | 200                                                        | 300          | 600          | 1,200                   |
|                                | Turndown (NG)              | Up to 16:1                                                 | Up to 16:1   | Up to 16:1   | Up to 16:1              |
|                                | Turndown (LP)              | Up to 16:1                                                 | Up to 16:1   | Up to 16:1   | Up to 16:1 <sup>b</sup> |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |                           | Models                                                     |                     |                     |                     |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------|------------------------------------------------------------|---------------------|---------------------|---------------------|
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |                           | RV (10, 25, 45, 75)   RVE (20, 40, 85, 150)   RVC (35, 65) |                     |                     |                     |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Housing Size              | 10   20                                                    | 25   35   40        | 45   65   85        | 75   150            |
| ELECTRIC HEAT                                                                                                                                                                                                                                                                                                                                                                                                                                                    | Minimum (kW) <sup>c</sup> | 5                                                          | 15                  | 35                  | 40                  |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Maximum (kW) <sup>c</sup> | 60                                                         | 60                  | 120                 | 230                 |
| OTHER HEAT                                                                                                                                                                                                                                                                                                                                                                                                                                                       | Air-source heat pump      | -                                                          | Option              | Option              | -                   |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Hot water                 | Option                                                     | Option              | Option              | Option              |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Steam coil                | -                                                          | Option              | Option              | Option              |
| ENERGY RECOVERY                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Polymer Enthalpy Wheel    | Option                                                     | Option              | Option              | Option              |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Aluminum Enthalpy Wheel   | -                                                          | Option              | Option              | Option              |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Polymer Enthalpy Core     | -                                                          | Option              | Option              | -                   |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Fiber Enthalpy Core       | -                                                          | Option              | Option              | -                   |
| CONTROLS                                                                                                                                                                                                                                                                                                                                                                                                                                                         | Full controls             | Standard                                                   | Standard            | Standard            | Standard            |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Heat-cool only            | Option                                                     | Option <sup>d</sup> | Option <sup>d</sup> | Option              |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Web user interface        | Standard                                                   | Standard            | Standard            | Standard            |
| CONSTRUCTION                                                                                                                                                                                                                                                                                                                                                                                                                                                     | Insulation                | 2" double-wall R-13                                        | 2" double-wall R-13 | 2" double-wall R-13 | 2" double-wall R-13 |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Exterior                  | Gray prepainted                                            | Gray prepainted     | Gray prepainted     | Gray prepainted     |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | Interior                  | Galvanized                                                 | Galvanized          | Galvanized          | Galvanized          |
| CERTIFICATION                                                                                                                                                                                                                                                                                                                                                                                                                                                    | AHRI 1060                 | Compliant                                                  | Compliant           | Compliant           | Compliant           |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | ASHRAE 90.1-2019          | Compliant                                                  | Compliant           | Compliant           | Compliant           |
|                                                                                                                                                                                                                                                                                                                                                                                                                                                                  | DOE 2023                  | Compliant                                                  | Compliant           | Compliant           | Compliant           |
| <p>Refer to Greenheck's CAPS<sup>®</sup> selection software or the Mechanical IOMs for additional detail.</p> <p>a Indicates total supply airflow. Variables such as energy recovery, cooling and heating options, design conditions, external static pressure, and others will affect these values.</p> <p>b LP Furnaces available on 600 and 800 mbh furnaces only</p> <p>c Max kW is dependent on unit voltage</p> <p>d Not available with the fiber core</p> |                           |                                                            |                     |                     |                     |