

Model DGX

MAKE-UP AIR UNITS WITH PACKAGED DX

Ultimate Efficiency. Minimal Impact.

Greenheck's Model DGX is the industry's first direct gas-fired make-up air unit with packaged direct expansion (PDX) cooling designed to comply with the new A2L refrigerant requirement. Engineered to safely integrate R-454B refrigerant, these units continue to deliver the benefits of direct gas-fired, 100% outdoor tempered air ventilation, heating, and cooling. Model DGX is available now for a more practical, sustainable, and highly efficient HVAC solution.



KEY FEATURES, BENEFITS, AND ADVANTAGES

Direct Gas-Fired Heating & PDX

- 100% outdoor air
- 92% efficient direct gas heating
- 25:1 turndown ratio
- 800-5,000 cfm, 3 in. wg
- 3-10 tons cooling

Superior Design & Efficiency

- Microchannel coils 40% more efficient, 40% smaller
- Uses 50% less refrigerant
- Modular design, flexible configuration
- Configurable supply fan options
- Galvanized steel construction
- Permator™ coating options

A2L Compliance & Safety

- Design mitigates A2L refrigerant risks
- UL 60335-2-40 Certified and ETL listed
- Low Global Warming Potential (GWP) reduces environmental impact
- EPA compliant HVAC systems
- Advanced safety features: leak detection and airflow sensors

TYPICAL APPLICATION: Commercial Kitchens

[greenheck.com](https://www.greenheck.com)

P.O. Box 410 | Schofield, WI 54476 | 715-359-6171 November 2024 © 2024 Greenheck Fan Corp.

 **GREENHECK**
Building Value in Air.