

Application

Model HBR-050 is a light duty round industrial backdraft damper with a flanged style frame. It allows air to be drawn into a draft relief application or to prevent backflow in an HVAC or a process application.

Ratings

Velocity

Up to 3000 fpm (15.2 m/s)

Pressure


Up to 6 in. wg (1.5 kPa) - differential pressure

Temperature

Up to 250°F (121°C)


Construction

	Standard	Optional
Frame Material	Galvanized steel	Painted, 304SS, or 316SS
Frame Type	Flanged channel	-
Blade Material	Galvanized steel	Painted, 304SS, 316SS
Blade Seals	None	-
Blade Stop	Pin	-
Blade Type	Round	-
Axle Bearing	Galvanized steel ball	-
Axle Material	Plated steel	316SS
Airflow	Horizontal	Vertical up, Vertical down
Paint Finishes	Mill finish	Hi Pro Polyester
Mounting Holes	None	On centerline, Straddle centerline




*Actual inside dimension

Advise air flow direction & counterbalance weight location when ordering



Diameter	Minimum Size	Maximum Size
Inches	7¼	24
mm	184	610




Diameter <i>D</i> Inches (mm)		Frame Depth <i>J</i> Inches (mm)	Frame & Flange Gauge (mm)	Flange Width <i>F</i> Inches (mm)	Square Axle Inches (mm)	Blade Thickness Gauge (mm)
Above	Through					
7¼ (184)	12 (305)	6 (152)	14 (2)	1.25 (32)	0.5 (12.7)	16 (1.5)
12 (305)	18 (457)	8 (203)	14 (2)	1.5 (32)	0.5 (12.7)	16 (1.5)
18 (457)	24 (610)	8 (203)	14 (2)	1.5 (32)	0.5 (12.7)	16* (1.5)

* with reinforcements

Performance Data

AMCA Test Figure 5.5


Figure 5.5 illustrates a plenum mounted damper. This configuration has the highest pressure drop because of high entrance and exit losses due to the sudden changes of area in the system.



Pressure Drop Data


This pressure drop data was conducted in accordance with AMCA Standard 500-D using Test Figure 5.5. All data has been corrected to represent standard air at a density of 0.075 lb./ft³ (1.2 kg/m³).

Actual pressure drop found in any HVAC system is a combination of many factors. This pressure drop information along with an analysis of other system influences should be used to estimate actual pressure losses for a damper installed in a given HVAC system.




Leakage Data

Damper leakage (with blade fully closed) varies based on the type of blade stops and low leakage seals applied. Model HBR-050 is available with no seals. Leakage testing was conducted in accordance with AMCA Standard 500-D and is expressed as cfm/ft² of damper face area. All data has been corrected to represent standard air at a density of 0.075 lb/ft³ (1.2 kg/m³).



Mounting Holes

The recommended bolt hole pattern is shown in the table below. Customer must specify bolt holes that are parallel to the axle centerline or that straddle the axle centerline as shown in the diagrams below. The factory can also provide bolt hole sizes and patterns other than those shown.



Recommended Bolt Hole Pattern
(Bolt Holes Parallel to Axle Centerline)

Diameter Inches (mm)		Number of Holes	Mounting Hole Diameter in. (mm) N	Bolt Circle Diameter L	Degrees Between Holes
Above	Through				
4 (102)	8 (203)	4	$\frac{3}{8}$ (9.5)	*	90
8.001 (203)	18 (457)	8	$\frac{7}{16}$ (11)	*	45
18.001 (457)	24 (610)	12	$\frac{7}{16}$ (11)	*	30

* Bolt Circle Diameter = Damper Diameter + Flange Height + $\frac{1}{4}$ in. (6 mm)

Document Links



[INSTALLATION](#)



[CATALOG](#)



[HD PRODUCT GUIDE](#)



[SELECTION GUIDE](#)



[SPECIFICATIONS](#)



[WARRANTY](#)