

Application

Model SMD-401EF is a class I leakage rated smoke damper with extruded aluminum blades and frame. High strength, streamlined extruded airfoil blades ensure the lowest resistance to airflow in HVAC systems. This model may be installed vertically (with blades running horizontal) or horizontally, and is rated for airflow and leakage in either direction.

Ratings

Leakage

UL 555S Leakage Class I

Velocity

Operational rated up to 3000 fpm (15.2 m/s). See chart below for size limitations.

Temperature

Maximum: 250°F (121°C) with all actuators

Pressure

Maximum: 6 in. wg (1.5 kPa)



* W & H dimensions furnished approximately ¼ in. (6mm) undersize.
 Note: This model is available with or without jackshaft.



See complete marking on product.
 UL 555S Classification R13317
 CAN/ULC S112.1 Classified Smoke Damper

Size Limitations


W x H	Minimum Size	Maximum Size	
		Single Section	Multiple Section
2000 fpm (10.2 m/s); 4 in. wg (1 kPa) pressure			
Inches	8 x 6	48 x 60	192 x 120
mm	203 x 152	1219 x 1524	4877 x 3048
3000 fpm (15.2 m/s); 6 in. wg (1.5 kPa) pressure			
Inches	8 x 6	36 x 48	144 x 96
mm	203 x 152	914 x 1219	3658 x 2438

Model SMD-401EF meets the requirements for smoke dampers established by:

- National Fire Protection Association
NFPA Standards, 90A, 92, 101, and 105
- International Building Codes (IBC)
- CSFM Californial State Fire Marshal
Leakage (Smoke) Listing (#3230-0981:0501)

Construction

Construction	Standard	Optional
Frame Material	Aluminum	-
Frame Thickness	.125 in. (3.2mm)	-
Frame Type	5 in. x 1 in. (127mm x 25mm) hat channel	Single Flange, Reverse Flange
Blade Material	Extruded Aluminum	-
Blade Action	Opposed	-
Blade Type	Airfoil	-
Blade Orientation	Horizontal	-
Linkage	Plated steel out of airstream, concealed in jamb	316SS
Axle Bearings	316SS	-
Axle Material	Plated steel	316SS
Blade Seals	Silicone	-
Jamb Seals	Stainless Steel	-
Mounting	Vertical	Horizontal



Note:


The frames are constructed with reinforced corners. Low profile head and sill are used on sizes less than 17 in. (432 mm) high for lower pressure drop and improved damper performance.

Options

- Clean wrap
- [OCI: Open closed indication switches](#)

Pressure Drop

AMCA Figure 5.2



12 in. x 12 in. (305mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.06
1500	0.13
2000	0.23
2500	0.35
3000	0.50
3500	0.68
4000	0.88

24 in. x 24 in. (610mm x 610mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.04
1500	0.10
2000	0.18
2500	0.28
3000	0.40
3500	0.54
4000	0.70

36 in. x 36 in. (914mm x 914mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.03
1500	0.06
2000	0.12
2500	0.18
3000	0.26
3500	0.35
4000	0.46


12 in. x 48 in. (305mm x 1219mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.06
1500	0.13
2000	0.23
2500	0.36
3000	0.51
3500	0.71
4000	0.93

48 in. x 12 in. (1219mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.03
1500	0.06
2000	0.10
2500	0.16
3000	0.23
3500	0.30
4000	0.39

AMCA Figure 5.3



12 in. x 12 in. (305mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.03
1500	0.07
2000	0.14
2500	0.21
3000	0.29
3500	0.39
4000	0.51

24 in. x 24 in. (610mm x 610mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.02
1500	0.04
2000	0.08
2500	0.13
3000	0.19
3500	0.26
4000	0.34

36 in. x 36 in. (914mm x 914mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.01
1500	0.02
2000	0.04
2500	0.06
3000	0.09
3500	0.13
4000	0.17


12 in. x 48 in. (305mm x 1219mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.03
1500	0.06
2000	0.11
2500	0.17
3000	0.25
3500	0.34
4000	0.45

48 in. x 12 in. (1219mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.01
1000	0.02
1500	0.04
2000	0.08
2500	0.12
3000	0.18
3500	0.24
4000	0.31

AMCA Figure 5.5



12 in. x 12 in. (305mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.04
1000	0.14
1500	0.31
2000	0.55
2500	0.86
3000	1.23
3500	1.67
4000	2.19

24 in. x 24 in. (610mm x 610mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.03
1000	0.12
1500	0.27
2000	0.48
2500	0.75
3000	1.07
3500	1.47
4000	1.91

36 in. x 36 in. (914mm x 914mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.03
1000	0.10
1500	0.22
2000	0.39
2500	0.61
3000	0.87
3500	1.19
4000	1.56

12 in. x 48 in. (305mm x 1219mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.03
1000	0.11
1500	0.25
2000	0.46
2500	0.72
3000	1.05
3500	1.43
4000	1.87


48 in. x 12 in. (1219mm x 305mm)

Velocity (fpm)	Pressure Drop (in. wg)
500	0.03
1000	0.11
1500	0.26
2000	0.46
2500	0.72
3000	1.02
3500	1.40
4000	1.83

Space Envelopes

Externally mounted actuators always require space outside of the damper sideplate or sleeve.


On dampers less than 18 in. (457mm) high, actuators may also require clearances above and/or below the damper. “B” and “T” dimensions are **worst case clearance requirements for some dampers less than 18 in. (457mm) high**. All dampers 18 in. (457mm) or more in height, do not require these worst case clearances. If space availability above or below the damper sleeve is limited, each damper size should be individually evaluated.




Actuator Type/Model	B	T
	Inches (mm)	
FSAF, FSAFB, and FSNF Series, Belimo	1½ in (38mm)	9¼ in (32mm)
FSLF Series, Belimo	8 in (203mm)	1½ in (32mm)

Multiple Section Dampers

Dampers larger than the maximum single section size, will be made up of a multiple equal size sections. Multiple section dampers can be jackshafted together so that all the sections operate together as shown below.



2 sections wide



4 sections wide
2 sections high



[INSTALLATION](#)



[CATALOG](#)



[DAMPER
SELECTION GUIDE](#)



[SPECIFICATIONS](#)



[WARRANTY](#)